









REVISIONS			
REV.	ECN NO.	DESCRIPTION	DATE
A1		\	2023.05.10



NOTE:

MAIN SPECIFICATION:

- Rated current: 50V AC, 6A
额定电流: 50V AC, 6A
- DIELECTRIC WITHSTAND VOLTAGE: 1000VAC
耐电压: 1000V MAX
- TEMPERATURE RANGE: -30 °C ~ 80 °C
使用温度: -30 °C ~ 80 °C
- CONTACT RESISTANCE: 30 MILLIONHM MAX
接触电阻: 30 MILLIONHM MAX(AFTER TEST 50mΩ Max)
- INSULATION RESISTANCE: 1000 MEGOHMS MIN.
绝缘阻抗: 1000 MEGOHMS MIN.
- AFTER DURABILITY(1000CYCLES)
寿命 (1000次)



PCB LAYOUT

IM NO.	ASSY P/N	ITEM	PART P/N	QTY	NAME	NOTE
		9	X3015-81-11N8	1PCS	锁片	COPPER ALLOY, 整个镀镍
		8	X3014W-31-21S8	1PCS	接地针	COPPER ALLOY, 镀锡
		7	X534WP-53-10A1	1PCS	3#端子	COPPER ALLOY, 镀金
		6	X534WP-52-10A1	2PCS	4#端子	
		5	X534WP-52-10A1	2PCS	2#端子	
		4	X534WP-51-10A1	2PCS	5#端子	
		3	X534WP-51-10A1	2PCS	1#端子	
		2	X534WP-11-N3B	1PCS	上盖	黑色PA66
		1	X534WP-01A-N3B	1PCS	底座	无logo, 黑色PA66

X±0.25	X.°±
.X±0.20	.X°±5°
.XX±0.15	.XX°±3°
.XXX±0.08	.XXX°±
UNITS:	mm

Customer P/N: \
Customer REV.: \
PART NO.:
APPD:
CHKD:
DRAW:

浙江创都电子科技有限公司		
TITLE: 5芯公头, 90度, 成品图		
DWG NO: XLR-G5-24W-JH		
SCALE	SHEET	REV.
1:1	1/1	A1

8 7 6 5 4 3 2 1

E D C B A

E D C B A

8 7 6 5 4 3 2 1