





RoHS

REVISIONS		
REV.	ECN NO.	DESCRIPTION
A1	2022/7/15	NEW DESIGN




NOTE:
MAIN SPECIFICATION:


- Rated current: 50V AC, 3A
额定电流: 50V AC, 3A
- DIELECTRIC WITHSTAND VOLTAGE: 1500VAC
耐电压: 1500V MAX
- TEMPERATURE RANGE: -30 °C ~ 80 °C
使用温度: -30 °C ~ 80 °C
- CONTACT RESISTANCE: 10 MILLIONHM MAX
接触电阻: 10 MILLIONHM MAX
- INSULATION RESISTANCE: 1500 MEGOHMS MIN.
绝缘阻抗: 1500 MEGOHMS MIN.
- AFTER DURABILITY(1000CYCLES)
寿命 (1000次)




Panel cut out



PCB layout(component-side)



Minimum installation spacing



序号	料号	名称	材料	数量	镀层	备注
3	X3014-31-21S8	接地片 (G#)	QSn6.5-0.1Y t=0.5	1	镀锡 (Sn)	
2	X313-1014+A	圆针	HPb59-1	3	镀金 (Au)	
1	X3014-00-N3B	基座 (BASE)	PA66 UL 94HB	1	黑色 (BALCK)	

X±0.20	X°±8°	Customer P/N:	浙江创都电子科技有限公司		
.X±0.15	.X°±5°	Customer REV.:			
.XX±0.07	.XX°±3°	PART NO.:	TITLE: XLR,3孔立式插座		
.XXX±0.05	.XXX°±1.5°	APPD:	DWG NO: XLR-09ZJ-NKJD-JH		
UNITS: mm		CHKD:	SCALE SHEET REV. 1:1 1/1 A1		
D TYPE	CUSTOMER D 客户图	DRAW:			

