



安装尺寸 MOUNTING MEASUREMENT



技术要求 Specification:

- 1、材料Material: Rubber shell:PA66 UL94V-0 PIN:H65 (Plating:NiSn)
- 2、额定电流Current rating: 3A max
- 3、额定电压 Voltage rating: 250V AC/DC
- 4、温度范围 Temperature range: -25℃ to +85℃
- 5、接触电阻 Contact resistance: $\leq 10m\Omega$
- 6、绝缘电阻 Insulation resistance: $\geq 1000M\Omega$
- 7、耐压 Withstand voltage: 1000V AC/minute
- 8、插针的固定力 Fixing force of pins: $\geq 20N$
- 9、适配的插头 Adaptable plug:HX25068-8Y~16Y (XAD-8Y~16Y)
- 10、适用基板厚度 Applicable PC board thickness: 1.6mm



B	15.0	17.5	20.0	22.5	25.0
A	7.5	10.0	12.5	15.0	17.5
孔数	8	10	12	14	16

未注公差表 UNNOTED TOLERANCE TABLE	设计 DRAWN BY	王鹏程	产品名称 PRODUCT NAME	针座 WAFER
≤ 3 ±0.1	审核 CHECKED BY	郑建银	产品型号 PRODUCT MODEL	XAD-8B~16B
≤ 10 ±0.2	批准 APPROVED BY	沈才义	红星代号 HONGXING NO	HX25068-8B~16B
≤ 20 ±0.3	日期 DATE	2021.01.23		
≤ 40 ±0.4	单位 UNIT	mm	版本 VERSION	B
≤ 80 ±0.5	比例 SCALE	2.5:1	页码 SHEET	1/1
视图 VIEW				

HX25 浙江红星电业有限公司
Zhejiang Hongxing Electrical Co., Ltd.