








修订 REV NO	标记 MARK	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
		NEW DWG		2016-03-12

性能：  
 额定电流：0.4A  
 额定电压：50V  
 耐电压：200V  
 接触电阻： $\leq 20m\Omega$   
 绝缘电阻：500M $\Omega$   
 工作温度：-20℃~+85℃

塑件（材质）：LCP, UL94V-0  
 锁扣（材质）：LCP, UL94V-0  
 插簧（材质）：磷青铜, 镀锡/镀金  
 焊片（材质）：磷青铜, 镀锡/镀金

孔位	A	B	C	D
4	2.4	4	9.6	10.3
5	3.2	4.8	10.4	11.1
6	4	5.6	11.2	11.9
7	4.8	6.4	12	12.7
8	5.6	7.2	12.8	13.5
9	6.4	8	13.6	14.3
10	7.2	8.8	14.4	15.1
11	8	9.6	15.2	15.9
12	8.8	10.4	16	16.7
13	9.6	11.2	16.8	17.5
14	10.4	12	17.6	18.3
15	11.2	12.8	18.4	19.1
16	12	13.6	19.2	19.9
17	12.8	14.4	20	20.7
18	13.6	15.2	20.8	21.5
19	14.4	16	21.6	22.3
20	15.2	16.8	22.4	23.1
21	16	17.6	23.2	23.9
22	16.8	18.4	24	24.7
23	17.6	19.2	24.8	25.5
24	18.4	20	25.6	26.3
25	19.2	20.8	26.4	27.1
26	20	21.6	27.2	27.9
27	20.8	22.4	28	28.7
28	21.6	23.2	28.8	29.5
29	22.4	24	29.6	30.3
30	23.2	24.8	30.4	31.1
31	24	25.6	31.2	31.9
32	24.8	26.4	32	32.7
33	25.6	27.2	32.8	33.5
34	26.4	28	33.6	34.3
35	27.2	28.8	34.4	35.1





深圳市华德共创科技有限公司  
 Shenzhen Huade co-create Technology Co., LTD  
 电话：0755-27111216 传真：0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		 		TITLE: 0.8mm FPC (B型)半包下接 产品名称: (H=2.5)			
X.X	$\pm 0.30$	X.X*	$\pm 3^\circ$	APPD: 核准:		PART NO: 产品编号: 0.8K-BX-nPWB(H=2.5)	
X.XX	$\pm 0.20$	X.XX*	$\pm 2^\circ$	CHECK: 王建业		DATE	SCALE
X.XXX	$\pm 0.10$	X.XXX*	$\pm 1^\circ$	DRAW: 黄艳兰		UNIT	CODE NUMBER
				2016-03-12	1:1	mm	A001