






版本 REV.	日期 DATE	ECN NO.	变更内容 DESCRIPTION	制图 DRAWN



PIN	尺寸 (mm)		
	A	B	C
-2*02A	2.00	6.00	4.80
-2*03A	4.00	8.00	6.80
-2*04A	6.00	10.00	8.80
-2*05A	8.00	12.00	10.80
-2*06A	10.00	14.00	12.80
-2*07A	12.00	16.00	14.80
-2*08A	14.00	18.00	16.80
-2*09A	16.00	20.00	18.80
-2*10A	18.00	22.00	20.80
-2*11A	20.00	24.00	22.80
-2*12A	22.00	26.00	24.80
-2*13A	24.00	28.00	26.80
-2*14A	26.00	30.00	28.80
-2*15A	28.00	32.00	30.80
-2*16A	30.00	34.00	32.80
-2*17A	32.00	36.00	34.80
-2*18A	34.00	38.00	36.80
-2*19A	36.00	40.00	38.80
-2*20A	38.00	42.00	40.80

**SPECIFICATIONS**

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material:Wafer PA46, UL94V-0  
PIN Brass Tin-plated

GENERAL TOLERANCE		制图 Mapping	H Y		料号 PART NO.	FG-PHD-2XNA		版本 REV.	A
X.±0.25	X.*±2'	审核 Audit	L P J		品名 TITLE	PHD直针 WAFER DIP TYPE		页次 SHEET	1/1
.X±0.20	.X*±1'	核准 Approved	L Z W		客户料号 CUTM. NO.				
.XX±0.15	.XX*±0.5'	单位 Units	MM	比例 SCALE	1:1				
.XXX±0.10	.XXX*±0.5'	深圳市富港科技有限公司							