


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.05.22	阿树



Specifications:


规格:
 Current rating:3A AC/DC
 额定电流: 3A AC/DC
 Voltage rating:250V AC
 额定电压: 250V AC
 Withstanding voltage:500V AC/MIN
 耐受电压: ≥500V AC/分钟
 Temperature range:-55°C~+105°C
 温度范围: -55°C~+105°C
 Insulation resistance:1000MΩMIN
 绝缘电阻: ≥1000MΩ
 Contact resistance:30mΩMAN
 接触电阻:≤30mΩ
 Material And FINISHED:
 材料和成本:
 INSULATOR:PBT UL 94V-0
 绝缘体: PBT UL 94V-0
 SHELL: SPCC-SD Plated Ni / Au / Sn
 外壳: 铁合金 镀镍/金/锡
 CONTACT MATERIAL:COPPER ALLOY
 触点材料: 铜合金

PART NO.:

X03 15 F I Z B 3
 ① ② ③ ④ ⑤ ⑥ ⑦

- ①Series NO.
- ②Row No.Pin No.XX-09;15;25;37
- ③Welding Board Angle :F-Female
- ④T: Traditional
- ⑤Planting Category: 1:1U' 2:2U' 3:3U' 4:5U' 5:15U' 6:30U' 7:AU Sn
- ⑥Color:B:Black W:White BL:Blue Y:Yellow G:Green R:Red
- ⑦1:TYPE-1; 2:TYPE-2; 3:TYPE-3; 4:TYPE-4; 6:TYPE-6

NO.OF CONTACT	A	B	C
09	30.80	24.99	16.35
15	39.20	33.30	24.75
25	53.05	47.04	38.35
37	69.40	63.50	54.75



铆合方式	TYPE-1:铆合	TYPE-6:直铆锁	TYPE-3:叉锁	TYPE-2:铆合锁螺丝
图式				

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: D-SUB
CHECKED		UNIT: mm/in	PART NO.: X0315FT7B3
APPROVED		SIZE: A4	DWG NO.: X-X0315FT7B3
			SCALE PAGE REVISION N/A 1/1 A1