







版次	变更摘要	日期
0	新产品发行	2017/1/20
1	料号更新	2024/09/10

序号	品名	材质
①	胶芯	LCP UL94V-0 本/黑/红色
②	端子	Brass/Tin plating
③	焊片	Brass/Tin plating

技术指标:

1. 工作温度: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
2. 额定电压: 200V DC/AC(rms).
3. 额定电流: 2.0A.
4. 接触电阻: $\leq 20\text{m}\Omega$.
5. 耐压值: 500V AC/minute.
6. 绝缘电阻: $\geq 1000\text{M}\Omega$.

CKT	DIM A	DIM B	DIM C
2	2.00	4.80	7.95
3	4.00	6.80	9.95
4	6.00	8.80	11.95
5	8.00	10.80	13.95
6	10.00	12.80	15.95
7	12.00	14.80	17.95
8	14.00	16.80	19.95
9	16.00	18.80	21.95
10	18.00	20.80	23.95
11	20.00	22.80	25.95
12	22.00	24.80	27.95
13	24.00	26.80	29.95
14	26.00	28.80	31.95
15	28.00	30.80	33.95
16	30.00	32.80	35.95
17	32.00	34.80	37.95
18	34.00	36.80	39.95
19	36.00	38.80	41.95
20	38.00	40.80	43.95



一般公差 (TOLERANCE)
 X ± 0.50 .XX ± 0.10
 X ± 0.20 .XXX ± 0.05
 ANGLES ± 1°

广东国连电子有限公司
 GUANGDONG GUOLIAN ELECTRONICS CO., LTD

品名 (TITLE) PH2.0卧贴 制图 (DR)

料号 (DWG.NO) 2.0-A-NPWB-R-0 校对 (CHKD)

比例 (SCALE) 单位 (UNITS) mm 审核 (APPD)

张数 (SHEET) 1 OF 1 SIZE A4 REV A