

1206（尺寸3.2×1.6mm） 1%精度 170种电阻常用阻值

0R	4.7R	24R	120R	620R	3.3K	16K	82K	430K	2.2M
1R	5.1R	27R	130R	680R	3.6K	18K	91K	470K	2.4M
1.1R	5.6R	30R	150R	750R	3.9K	20K	100K	510K	2.7M
1.2R	6.2R	33R	160R	820R	4.3K	22K	110K	560K	3M
1.3R	6.8R	36R	180R	910R	4.7K	24K	120K	620K	3.3M
1.5R	7.5R	39R	200R	1K	5.1K	27K	130K	680K	3.6M
1.6R	8.2R	43R	220R	1.1K	5.6K	30K	150K	750K	3.9M
1.8R	9.1R	47R	240R	1.2K	6.2K	33K	160K	820K	4.3M
2R	10R	51R	270R	1.3K	6.8K	36K	180K	910K	4.7M
2.2R	11R	56R	300R	1.5K	7.5K	39K	200K	1M	5.1M
2.4R	12R	62R	330R	1.6K	8.2K	43K	220K	1.1M	5.6M
2.7R	13R	68R	360R	1.8K	9.1K	47K	240K	1.2M	6.2M
3R	15R	75R	390R	2K	10K	51K	270K	1.3M	6.8M
3.3R	16R	82R	430R	2.2K	11K	56K	300K	1.5M	7.5M
3.6R	18R	91R	470R	2.4K	12K	62K	330K	1.6M	8.2M
3.9R	20R	100R	510R	2.7K	13K	68K	360K	1.8M	9.1M
4.3R	22R	110R	560R	3K	15K	75K	390K	2M	10M

