


版本/version	变更内容/ECN	工程确认confirmation	日期Date



技术要求:  
 1.原料及电镀  
 11、材料: COPPER H62, 厚度1mm;  
 12、表面镀镍3-5um, 盐雾24H  
 2.包装要求: 卷带;  
 3.不允许有毛刺, 锐边等外观缺陷, 具体以 ISTR签样为准;  
 4.未注尺寸参考3D数据: 未注尺寸公差满足QC/T268-199;  
 5.产品符合ELV要求和Q/MAP 3702;  
 6.需求规范: QPR\_SOLDERING PROCESSES\_A2C00052907AAA VERSION E  
 7.零件应保持清洁, 表面无脏污和异物;  
 满足清洁度规范 CCC A(F8/G7/H6/100)PER ISO 16232:2018 、  
 CCC A(F10/G9/H8/16/15/K4/L-N00) PER ISO16232:2018  
 根据第7.4.4条(超声波振动)提取方法。根据第9.2.3段的分析方法。  
 8.性能要求: 焊接性能符合IPC-A-610H三级标准;  
 9.法规要求: 产品符合ELV标准  
 10. 载流能力: 25A  
 Current capacity: 25A  
 11. 符合RoHS、REACH环保要求;  
 RoHS、REACH Compliance

品牌(BRAND)	<b>Yiyuanxny®</b>	页码(SHEET)	1/1	单位(UNIT):MM
		版本(REV)	A1	比例(SCALE)
工厂(FACTORY)	广东怡远科技有限公司 GUANGDONG YIYUAN TECHNOLOGY CO.,LTD	日期(DATE)	2021.10.12	$\varnothing$ $\square$
		设计(DESIGN)	LUO	未注公差 TOLERANCE UNSPECIFIED
品名(ITEM NO)	10x4x1MM Brass Ni plating Busbar	审核(CHECKED)	ROGER LI	X.X ±0.15 X.XX ±0.10 X.XXX ANG. ±2'
料号(PART NO)	YTC-M1041-BNR	核准(APPROVED)	ROC ZHAO	

These drawings and specifications are Yiyuan Technology Co Ltd.The property should not be copied. Without Yiyuan Technology Co. Ltd.Prior written consent to copy or use in any way. Email at info@yiyuanxny.com