




REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	A2	REVISED AS PER ECN-26-370067	09FEB2026	YS WZ



- NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)
1. BRASS
 2. GOLD PL. 3 MIN. THICK OVER NICKEL PL. 50 MIN. THICK OVER COPPER PL. 50 MIN. THICK
 3. BERYLLIUM COPPER
 4. GOLD PL. 30 MIN. THICK OVER NICKEL PL. 50 MIN. THICK OVER COPPER PL. 50 MIN. THICK
 5. PTFE

- SPECIFICATIONS:
1. IMPEDANCE: 50 Ohm
 2. FREQUENCY: DC to 18GHz
 3. VSWR/RL: 1.3 max./ 17.69 dB min.
 4. CONTACT RESISTANCE:
CENTER: 3 milliohms max.
OUTER: 2 milliohms max.
 5. TEMPERATURE RANGE: -65°C TO +165°C
 6. DURABILITY: 500 cycles min.
 7. ENGAGEMENT AND DISENGAGEMENT FORCE:
ENGAGEMENT: 2 in-lbs max.
DISENGAGEMENT: 2 in-lbs max.
 8. ROHS COMPLIANT.
 9. PACKAGING DETAIL IS IN PAGE 2.
 10. PRODUCT WEIGHT: 4.2 g

UNLESS OTHERWISE SPECIFIED TOLERANCES

0.5-6	= ±0.2
6-30	= ±0.4
30-120	= ±0.6
120-315	= ±1
315-1000	= ±1.6
1000-2000	= ±2.4

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
	ANGLES ± 5
MATERIAL	FINISH
-	-

QTY	NOTE	DESCRIPTION	ITEM
1	NOTE 2	COVER	7
1	NOTE 4	CONTACT PIN	6
1	NOTE 4	CONTACT PIN	5
1	NATURAL	INSULATOR	4
1	NOTE 2	BODY	3
1	NATURAL	INSULATOR	2
1	NOTE 2	HOUSING	1
2484786-1	FINSIH	MATERIAL	DESCRIPTION
			ITEM

DWN	27MAR2024	SIDDHARTH SINGH	
CHK	27MAR2024	ERIC DAI	
APVD	27MAR2024	WENKE HE	
PRODUCT SPEC	108-161323	SMA JACK RA SMD PIN THRU HOLE 18 GHz	
APPLICATION SPEC	-	-	
WEIGHT	-	SIZE	CAGE CODE
CUSTOMER DRAWING	A2	00779	C-2484786
SCALE	1:1	DRAWING NO	RESTRICTED TO
SHEET	1 of 2	REV	A2

4


3

2



1

© - TE Connectivity. All Rights Reserved.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-





← Place a cardboard on the top of the boxes.



← Pack 100 pcs per tray. There is 1 tray per inner box, total of 3 inner boxes.



← Place a cardboard on the bottom of the boxes.



NOTE: 1. 100 pcs / Tray, 1 tray = 1 inner box
2. 3 inner box = 300 pcs

RoHS, REACH Compliance

UNLESS OTHERWISE SPECIFIED TOLERANCES

- 0.5-6 = ±0.2
- 6-30 = ±0.4
- 30-120 = ±0.6
- 120-315 = ±1
- 315-1000 = ±1.6
- 1000-2000 = ±2.4

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SIDDHARTH SINGH 27MAR2024	TE TE Connectivity	
DIMENSIONS: mm		CHK ERIC DAI 27MAR2024		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD WENKE HE 27MAR2024	NAME SMA JACK RA SMD PIN THRU HOLE 18 GHz	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± 5		PRODUCT SPEC 108-161323	APPLICATION SPEC -	
MATERIAL -		FINISH -	WEIGHT 0	RESTRICTED TO -
		SIZE A2	CAGE CODE 00779	DRAWING NO C-2484786
		CUSTOMER DRAWING		SCALE 1:1 SHEET 2 of 2 REV A2