




版本/version	变更内容/ECN	工程确认confirmation	日期Date



技术要求:
 1.原料及电镀
 11、材料: COPPER T2, 厚度3mm
 12、表面镀镍底3~5um, 盐雾24H
 2.包装要求: 卷带;
 3.不允许有毛刺, 锐边等外观缺陷, 具体以 ISTR 签样为准;
 4.未注尺寸参考 3D 数据: 未注尺寸公差满足 QC/T268-199;
 5.产品符合 ELV 要求和 Q/ MAP 3702;
 6.需求规范: QPR_SOLDERING PROCESSES_A2C00052907AAA VERSION E
 7.零件应保持清洁, 表面无脏污和异物;
 满足清洁度规范 CCC A(F8/G7/H6/100)PER ISO 16232:2018 、
 CCC A (F10/G9/H8/16/J5/K4/L-N00) PER ISO16232:2018
 根据第 7.4.4 条(超声波振动)提取方法。根据第 9.2.3 段的分析方法,
 8.性能要求: 焊接性能符合 IPC-A-610H 三级标准;
 9.法规要求: 产品符合 ELV 标准
 10. 载流能力: 50A
 Current capacity: 50A
 11. 符合 RoHS、REACH 环保要求;
 RoHS、REACH Compliance

品牌(BRAND)	Yiyuanxny [®]	页码(SHEET)	1/1	单位(UNIT):MM
		版本(REV)	A1	比例(SCALE)
工厂(FACTORY)	广东怡远科技有限公司 GUANGDONG YIYUAN TECHNOLOGY CO., LTD	日期(DATE)	2021.10.12	\varnothing \square
		设计(DESIGN)	LUO	未注公差 TOLERANCE UNSPECIFIED
品名(ITEM NO)	5x3x3MM T2 Ni plating Busbar	审核(CHECKED)	ROGER LI	X.X ±0.15 X.XX ±0.10 X.XXX ANG. ±2'
料号(PART NO)	YTC-M533-ZNR	核准(APPROVED)	ROC ZHAO	

These drawings and specifications are Yiyuan Technology Co Ltd.The property should not be copied. Without Yiyuan Technology Co. Ltd.Prior written consent to copy or use in any way. Email at info@yiyuanxny.com