



Mounting hole	Ø22.5mm
Switch standard	22mm

Symbol	Manufacturer	Signalling method	U _{sup} [V DC]	U _{sup} [V AC]	Current consumption [mA]	Operating temperature [°C]	IP rating	Manufacturer series	Colour
CM22-S	COBI ELECTRONIC	pulsed tone	24...230	24...230	25	-20...60	IP54	CM22	black
CM22-SLR	COBI ELECTRONIC	pulsed tone	24...230	24...230	25	-20...60	IP54	CM22	red
LPCZSA	LOVATO ELECTRIC	buzzer	9...15	9...15	-	-	IP40	-	black
LPCZSAIP	LOVATO ELECTRIC	buzzer	9...15	9...15	-	-	IP66	-	black
LPCZSB	LOVATO ELECTRIC	buzzer	18...30	18...30	-	-	IP40	-	black
LPCZSBIP	LOVATO ELECTRIC	buzzer	18...30	18...30	-	-	IP66	-	black
LPCZSE	LOVATO ELECTRIC	buzzer	85...140	85...140	-	-	IP40	-	black
LPCZSEIP	LOVATO ELECTRIC	buzzer	85...140	85...140	-	-	IP66	-	black
LPCZSM	LOVATO ELECTRIC	buzzer	185...265	185...265	-	-	IP40	-	black
LPCZSMIP	LOVATO ELECTRIC	buzzer	185...265	185...265	-	-	IP66	-	black



Electronic Components

— EST. 1989 —

TRANSFER MULTISORT ELEKTRONIK SP. Z O.O.

ul. Ustronna 41, 93-350 Łódź, Poland

NIP: 729-010-89-84, VAT UE: PL7290108984

District Court for Łódź-Śródmieście in Łódź

KRS:0000165815

Amount of share capital: 3 300 000 PLN

Contact us:

Tel.: +48 42 645 54 44

Fax.: +48 42 645 54 70

E-mail: export@tme.eu

JOIN US:





Product Information Management: www.parcats.eu