





REV.	ECN NO.	DESCRIPTION	DRAW	APPD.	LRT DATE
A	----	新版本发行	孟生	刘静	2019.08.08
A1	----	新版本发行	孟生	刘静	2019.08.18



NOTES:

SPECIFICATION:

1. CURRENT RATING: 3.0A MAX
2. VOLTAGE: 100 VAC
3. TEMPERATURE RANGE: -30 °C ~ 85 °C
4. CONTACT RESISTANCE: 40 MILLIONHM MAX
5. INSULATION RESISTANCE: 100 MEGOHMS MIN.
6. LNSERTION FORCE : 5N~20N
7. UNMATING FORCE: 8N~20N
8. DURABILITY: 8,000 CYCLES



RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm



NO.	DESCRIPTION	MATERIAL	REMARKS	QTY
6	SHELL	STAINLESS STEEL	NI Plated	1PCS
5	SHIELDING PLATE	STAINLESS STEEL	---	1PCS
4	MD	HIGH TEMPERATURE PLASTIC	BLACK	1PCS
3	CONTACT	COPPER ALLOY	Au/Ni Plated	1SET
2	CONTACT	COPPER ALLOY	Au/Ni Plated	1SET
1	HOUSING	HIGH TEMPERATURE PLASTIC	BLACK	1PCS

PIN	SIGNAL NAME	PIN	SIGNAL NAME
A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND

TOLERANCE	NAME(INTENDED USE)	REMARKS		
X.X ±0.30 X.* ± 2°	PART NO. TYPE16-NI N1-MD651-Z	东莞市高钺达电子科技有限公司 惠州市高钺达光电科技有限公司		
.XX ±0.20 .X* ± 1°		TITLE: USB C F TYPE单排SMT四脚插板 一次成型带钢片 6.5 无柱		
.XXX ±0.10 .XX* ±0.5°	APPD: 刘静	DRAWG NO.		
UNITS mm	CHED: 张工	SCALE 1:1	SHEET 1/1	REV. A1
MATERILA	DRAW: 孟生			