

Description

Length: 3/16", thread: 2-56, pan head, corrosion resistant steel, coarse thread, MS51957 series screw

* Manufacturer certifications are shipped with your order FREE of charge

Order this part online

Additional Information

SKU / Model:	MS519572
Minimum Qty (MOQ):	100
NSN:	5305-00-054-5636
Schedule B:	7318.22.0000
ECCN:	EAR99
National Motor Freight:	093486, Bolts,nuts Or Screws, Noi (sub 3)



* See page 2 for technical characteristics

P/N MS51957-2 Specifications

Thread Class:	2a
Thread Direction:	Right-hand
Thread Length:	0.121 Inches Minimum And 0.188 Inches Maximum
Fastener Length:	0.157 Inches Minimum And 0.188 Inches Maximum
Head Style:	Pan
Head Diameter:	0.155 Inches Minimum And 0.167 Inches Maximum
Head Height:	0.053 Inches Minimum And 0.062 Inches Maximum
Internal Drive Style:	Cross Recess Type 1
Nominal Thread Diameter:	0.086 Inches
Thread Quantity Per Inch:	56
Minimum Tensile Strength:	80000 Pounds Per Square Inch
Screw Material:	Steel Comp 301 Or Steel Comp 302 Or Steel Comp 302b Or Steel Comp 303 Or Steel Comp 303se Or Steel Comp 304 Or Steel Comp 304l Or Steel Comp 305 Or Steel Comp 308 Or Steel Comp 309 Or Steel Comp 309s Or Steel Comp 310 Or Steel Comp 310s Or Steel Comp 314 Or Steel Comp 316 Or Steel Comp 316l Or Steel Comp 317 Or Steel Comp 321 Or Steel Comp 347 Or Steel Comp 348 Or Steel Comp 384 Or Steel Comp 385
Screw Surface Treatment:	Passivate
Screw Surface Treatment Document And Classification:	Qq-p-35 Fed Spec Single Treatment Response
Thread Series Designator:	Unc
Nondefinitive Spec/std Data:	1 Type Or 9c Style

How to Order

Order this machine screw from our inventory online by visiting <https://military-fasteners.com/screws/machine+screws/MS51957-2> and selecting the quantity you want then click "add to cart". Once items are in your cart you can check out [here](#) to complete your order.