


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW RELEASE PER ECO-14-009837	07-01-14	DM	DM



- 4. PART NO. DRC40-GKT
- 3. THICKNESS: 3.18 [.125]
- 2. TEMPERATURE RATING: -57°C TO +107°C [-70°F TO +225°F]
- 1. THIS PART IS USED ON
DRC12-40PX(E)-XXXX RECEPTACLE
WHERE X=A,B,C,D KEYS AND XXXX=MODIFICATION

2014

RELEASED FOR PUBLICATION

THIS DRAWING IS UNPUBLISHED.

ALL RIGHTS RESERVED.

© COPYRIGHT 2014 BY TE CONNECTIVITY

DIMENSIONS: MM [INCH]	DWN	D. MEYER 01JUL2014	MATERIAL	CLD CELL SPONGE	FINISH	BLACK
	CHK	D. HASIBUAN 01JUL2014				
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	D. MEYER 01JUL2014				
0 PLC ±	PRODUCT SPEC	NAME				GASKET, RECEPTACLE, 40PIN DRC SERIES
1 PLC ±	APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
2 PLC ± 0.63 [.025]		A 4	4AFU8	C = DRC40-GKT	-	
3 PLC ±	WEIGHT	.907 G		SCALE	NONE	SHEET 1 OF 1
4 PLC ±	Customer Drawing				REV	A
ANGLES ± 5°						