



MILITARY ★ FASTENERS

Military-Fasteners.com

P/N MS51957-4

Description

length: 5/16", thread: 2-56, pan head screw, corrosion resistant steel, coarse thread, MS51957 series screw

* Manufacturer certifications are shipped with your order FREE of charge

Order this part online

Additional Information

SKU / Model:	MS519574
Minimum Qty (MOQ):	100
NSN:	5305-00-054-5638
Schedule B:	7318.15.6080
ECCN:	EAR99
National Motor Freight:	093486, Bolts,nuts Or Screws, Noi (sub 3)



* See page 2 for technical characteristics

P/N MS51957-4 Specifications

Thread Class:	2a
Thread Direction:	Right-hand
Thread Length:	0.276 Inches Minimum And 0.312 Inches Maximum
Fastener Length:	0.281 Inches Minimum And 0.312 Inches Maximum
Head Style:	Pan
Head Diameter:	0.155 Inches Minimum And 0.167 Inches Maximum
Head Height:	0.053 Inches Minimum And 0.062 Inches Maximum
Internal Drive Style:	Cross Recess Type 1
Nominal Thread Diameter:	0.086 Inches
Thread Quantity Per Inch:	56
Minimum Tensile Strength:	80 Pounds Per Square Inch
Screw Material:	Steel Comp 316
Screw Material Document And Classification:	66 Fed Std Single Material Response
Screw Surface Treatment:	Passivate
Screw Surface Treatment Document And Classification:	Qq-p-35 Fed Spec Single Treatment Response
Thread Series Designator:	Unc

How to Order

Order this machine screw from our inventory online by visiting <https://military-fasteners.com/screws/machine+screws/MS51957-4> and selecting the quantity you want then click "add to cart". Once items are in your cart you can check out [here](#) to complete your order.