





REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.1.14	阿树










d 0.10
ALL SOLDERTAIL
& FITTING NAIL

VIEW D
SCALE 4:1



RECOMMENDED OPERATING FLOW:
MATE: 1 2
UNMATE: 3 4



AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	
CHECKED		UNIT:	mm/in
APPROVED		SIZE:	A4

MODEL TYPE: 0.50mm BTB Connector		
PART NO.: X1302WVS-67FB-LPV01		
DWG NO.: X-X1302WVS-67FB-LPV01		
SCALE N/A	PAGE 1/3	REVISION A1



1

2


3

4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.1.14	阿树



AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树
CHECKED	
APPROVED	

VIEW:	
UNIT:	mm/in
SIZE:	A4

MODEL TYPE: 0.50mm BTB Connector		
PART NO.: X1302WVS-67FB-LPV01		
DWG NO.: X-X1302WVS-67FB-LPV01		

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	3/3	A1

1

2

3

4