







REV.	DATE	ECN NO.	MODIFICATION	APPROVER
AO	2021/07/03		NEW	Jason



SPECIFICATIONS:  
 1.Current Rating: 1A DC  
 2.Voltage Rating:125V AC/DC  
 3.Insulation Resistance:100MΩ min  
 4.Contact resistance:20mΩ Max  
 5.Dielectric Withstanding:500V/1minute  
 5.Operating Temperature:-25°C~+85°C  
 Material:  
 1.Housing:Thermoplastic,UL94V-0 Natural  
 2.Contact:Copper alloy, Tin plated  
 Major Dimension:▼  
 Lead free and ROHS compliant product



LOCK CONFIGURATION (锁扣位置)



CKT	DIM A	DIM B	DIM C
2	1.25	3.20	4.30
3	2.50	4.45	5.55
4	3.75	5.70	6.80
5	5.00	6.95	8.05
6	6.25	8.20	9.30
7	7.50	9.45	10.55
8	8.75	10.70	11.80
9	10.00	11.95	13.05
10	11.25	13.20	14.30
11	12.50	14.45	15.55
12	13.75	15.70	16.80
13	15.00	16.95	18.05
14	16.25	18.20	19.30
15	17.50	19.45	20.55
16	18.75	20.70	21.80
17	20.00	21.95	23.05
18	21.25	23.20	24.30
19	22.50	24.45	25.55
20	23.75	25.70	26.80

GENERAL TOLERANCE			UNITS	NAME(INTENDED USE)		ATOM® 深圳市爱特姆科技有限公司 SHENZHEN ATOM TECHNOLOGY CO., LTD.
SELECT	✓		mm	WF		
TOL. ON.	1	2	MAT'L	PART NO.(INTENDED USE)		TITLE: Customer Drawing For Wafer1.25mm XP DIP 180°W=3.2
X.XXX	±0.10	±0.15	FINISH	WF125**-07***		DWG NO.: ATOM-A06955
X.XX	±0.15	±0.20		Q'TY	APPD: Abel	
X.X	±0.20	±0.25	CHKD: Tom		DR: XCF	SHEET: 1/1
X.	±0.25	±0.30	ANGLE ±2'			REV: AO