

| 修订 | 标记 | 修改摘要 | 签名 | 日期 |
|-----|------|----------------------|-----------|------------|
| REV | MARK | REVISION DESCRIPTION | SIGNATURE | DATE |
| AO | | NEW DWG | | 2016-03-12 |









TABLE:

| P位 | Dimension mm | |
|-----|--------------|-------|
| | A | B |
| 2P | 1.25 | 7.65 |
| 3P | 2.54 | 8.90 |
| 4P | 3.75 | 10.15 |
| 5P | 5.00 | 11.30 |
| 6P | 6.25 | 12.65 |
| 7P | 7.50 | 13.90 |
| 8P | 8.75 | 15.15 |
| 9P | 10.00 | 16.40 |
| 10P | 11.25 | 17.65 |
| 11P | 12.50 | 18.90 |
| 12P | 13.75 | 20.15 |
| 13P | 15.00 | 21.40 |
| 14P | 16.25 | 22.65 |
| 15P | 17.50 | 23.90 |
| 16P | 23.75 | 30.15 |

NOTE:
 Current rating:1A AC,DC
 Voltage rating:125V AC,DC
 Temperature range:-25°C~+85°C
 Insulation resistance:100MΩ/Min
 Withstanding voltage:500V AC/minute
 Contact resistance:20mΩ/Max
 PIN:Brass/Gold-Plated
 Suitable With:A1254HF Series Housing



深圳市华德共创科技有限公司
 Shenzhen Huade co-create Technology Co.,LTD
 电话: 0755-27111216 传真: 0755-29940187

| -TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表 | | TITLE: 产品名称: 1.25间距超薄针座 | |
|---|------------|----------------------------|---------------------------------|
| X.X ±0.30 | X.X* ±3° | APPD: 核准: | PART NO: 产品编号: 1.25K-CB-nPWB |
| X.XX ±0.20 | X.XX* ±2° | CHECK: 校对: 王建业 | DATE SCALE UNIT CODE NUMBER |
| X.XXX ±0.10 | X.XXX* ±1° | DRAW: 绘图: 黄艳兰 | 2014-06-18 1:1 mm A001 |