







REV.	DATE	ECN NO.	MODIFICATION	APPROVER
A0	2019.07.09	***	NEW	Abel
A1	2022.10.24	RD00322102402	更新D尺寸管控	Abel



3P示意图



2P示意图



2P结构样式

CKT	A	B	C	D
2	2.50	5.70	7.30	3.00
3	5.00	8.20	9.80	5.00
4	7.50	10.70	12.30	5.00
5	10.00	13.20	14.80	7.50
6	12.50	15.70	17.30	10.00
7	15.00	18.20	19.80	12.50
8	17.50	20.70	22.30	12.50
9	20.00	23.20	24.80	12.50
10	22.50	25.70	27.30	12.50
11	25.00	28.20	29.80	12.50
12	27.50	30.70	32.30	12.50
13	30.00	33.20	34.80	12.50
14	32.50	35.70	37.30	12.50
15	35.00	38.20	39.80	12.50
16	37.50	40.70	42.30	12.50

Material:
Housing: Thermoplastic,UL94V-0
Electrical:
1.Current Rating: 3A AC,DC
2.Voltage Rating: 250V AC,DC
3.Contact Resistance: 20mΩ MAX
4.Dielectric Withstanding Voltage: 1000V AC
5.Insulation Resistance: 1000MΩ MIN
6.Operating Temperature: -25°C~+85°C
Lead free and ROHS compliant product.

GENERAL TOLERANCE				UNITS	NAME(INTENDED USE)	
SELECT	✓			mm	HOUSING	
TOL.	1	2	3	MAT'L	PART NO.(INTENDED USE)	
X.XXX	±0.10	±0.15	±0.20	FINISH	HO250**-01***	
X.XX	±0.15	±0.20	±0.25		TITLE:Customer' drawing for HOUSING 2.5 XP	
X.X	±0.20	±0.25	±0.30	Q'TY	PA66 白色 胶芯 带扣	
X.	±0.25	±0.30	±0.50		DWG NO.: ATOM-A07138	
ANGLE	±2'				DR: Ling	SCALE SHEET REV.
						1:1 1/1 A1

ATOM 深圳市爱特姆科技有限公司
SHENZHEN ATOM TECHNOLOGY CO., LTD.