






RoHS Compliant



No. of Contacts	DIM A	DIM B	DIM C
2	1.25	3.85	5.75
3	2.50	5.10	7.00
4	3.75	6.35	8.25
5	5.00	7.60	9.50
6	6.25	8.85	10.75
7	7.50	10.10	12.00
8	8.75	11.35	13.25
9	10.00	12.60	14.50
10	11.25	13.85	15.75
11	12.50	15.10	17.00
12	13.75	16.35	18.25
13	15.00	17.60	19.50
14	16.25	18.85	20.75
15	17.50	20.10	22.00
18	21.25	23.85	25.75
20	23.75	26.35	28.25



PCB LAYOUT

产品规格:

1 材质

- 1.1 胶芯: 高温尼龙
- 1.2 端子: 黄铜镀锡

2 电气性能

- 2.1 额定电压 50V AC、DC
- 2.2 额定电流 1 A AC、DC
- 2.3 接触阻抗 < 30 mΩ
- 2.4 绝缘阻抗 > 100MΩ
- 2.5 耐压 > 500 V AC

深圳市敏连达科技有限公司 Shenzhen Minlianda Technology Co.,Ltd.		品名 (ITEM NO)	GH 立贴		
		料号 (PART NO)	MLD-GH1.25-XX-L		
单位 (UNIT): MM	未注公差 TOLERANCE UNSPECIFIED	版次 (REV): A/O	页次 (PAGE): 1/1	设计 (DESIGN)	柯南
比例 (SCALE) 1:1	X.X ± 0.38 X.XX ± 0.20 X.XXX ± 0.10 X' ± 5' X.X' ± 2'	模号 (MODEL NO)	审核 (CHECKED) 邱敏		
		图号 (DWG NO)	MLD-2509031032	核准 (APPROVED)	陈镇