








| 修 订 | 标 记  | 修 改 描 要              | 签 名       | 日 期        |
|-----|------|----------------------|-----------|------------|
| REV | MARK | REVISION DESCRIPTION | SIGNATURE | DATE       |
| NO  |      | NEW DWG              |           | 2016-03-12 |

| PIN | DIM A | DIM B | DIM C | DIM D | DIM E | DIM F |
|-----|-------|-------|-------|-------|-------|-------|
| 4   | 3.00  | 5.10  | 5.00  | 11.00 | 9.20  | 10.30 |
| 5   | 4.00  | 6.10  | 6.00  | 12.00 | 10.20 | 11.30 |
| 6   | 5.00  | 7.10  | 7.00  | 13.00 | 11.20 | 12.30 |
| 7   | 6.00  | 8.10  | 8.00  | 14.00 | 12.20 | 13.30 |
| 8   | 7.00  | 9.10  | 9.00  | 15.00 | 13.20 | 14.30 |
| 9   | 8.00  | 10.10 | 10.00 | 16.00 | 14.20 | 15.30 |
| 10  | 9.00  | 11.10 | 11.00 | 17.00 | 15.20 | 16.30 |
| 11  | 10.00 | 12.10 | 12.00 | 18.00 | 16.20 | 17.30 |
| 12  | 11.00 | 13.10 | 13.00 | 19.00 | 17.20 | 18.30 |
| 13  | 12.00 | 14.10 | 14.00 | 20.00 | 18.20 | 19.30 |
| 14  | 13.00 | 15.10 | 15.00 | 21.00 | 19.20 | 20.30 |
| 15  | 14.00 | 16.10 | 16.00 | 22.00 | 20.20 | 21.30 |
| 16  | 15.00 | 17.10 | 17.00 | 23.00 | 21.20 | 22.30 |
| 17  | 16.00 | 18.10 | 18.00 | 24.00 | 22.20 | 23.30 |
| 18  | 17.00 | 19.10 | 19.00 | 25.00 | 23.20 | 24.30 |
| 19  | 18.00 | 20.10 | 20.00 | 26.00 | 24.20 | 25.30 |
| 20  | 19.00 | 21.10 | 21.00 | 27.00 | 25.20 | 26.30 |
| 21  | 20.00 | 22.10 | 22.00 | 28.00 | 26.20 | 27.30 |
| 22  | 21.00 | 23.10 | 23.00 | 29.00 | 27.20 | 28.30 |
| 23  | 22.00 | 24.10 | 24.00 | 30.00 | 28.20 | 29.30 |
| 24  | 23.00 | 25.10 | 25.00 | 31.00 | 29.20 | 30.30 |
| 25  | 24.00 | 26.10 | 26.00 | 32.00 | 30.20 | 31.30 |
| 26  | 25.00 | 27.10 | 27.00 | 33.00 | 31.20 | 32.30 |
| 27  | 26.00 | 28.10 | 28.00 | 34.00 | 32.20 | 33.30 |
| 28  | 27.00 | 29.10 | 29.00 | 35.00 | 33.20 | 34.30 |
| 29  | 28.00 | 30.10 | 30.00 | 36.00 | 34.20 | 35.30 |
| 30  | 29.00 | 31.10 | 31.00 | 37.00 | 35.20 | 36.30 |
| 31  | 30.00 | 32.10 | 32.00 | 38.00 | 36.20 | 37.30 |
| 32  | 31.00 | 33.10 | 33.00 | 39.00 | 37.20 | 38.30 |
| 33  | 32.00 | 34.10 | 34.00 | 40.00 | 38.20 | 39.30 |
| 34  | 33.00 | 35.10 | 35.00 | 41.00 | 39.20 | 40.30 |
| 35  | 34.00 | 36.10 | 36.00 | 42.00 | 40.20 | 41.30 |
| 36  | 35.00 | 37.10 | 37.00 | 43.00 | 41.20 | 42.30 |



Electrical  
 rated current:0.5A AC(rms)/DC  
 nominal voltage:50V AC(rms)/DC  
 Dielectric Withstanding Voltage:500V AC/rms  
 Contact Resistance:≤20 mΩ max(initial)  
 Insulation Resistance:800 MΩ min  
 Operating Temp:-20℃~+85℃



PC BOARD LAYOUT



**深圳市华德共创科技有限公司**  
 Shenzhen Huade co-create Technology Co.,LTD  
 电话：0755-27111216 传真：0755-29940187

| -TOLERANCES-<br>UNLESS OTHERWISE SPECIFIED<br>公差参数表 |            | TITLE:<br>产品名称: 1.0mm FPC 半包抽拉下接式H=2.5 |                                |
|---|------------|--|--------------------------------|
| X.X ±0.30   | X.X* ±3°   | APPD:<br>核准:                           | PART NO:<br>产品编号: 1.0K-FX-nPWB |
| X.XX ±0.20  | X.XX* ±2°  | CHECK:<br>校对: 王建业                      | DATE SCALE UNIT CODE NUMBER    |
| X.XXX ±0.10   | X.XXX* ±1° | DRAW:<br>绘图: 黄艳兰                       | 2014-03-16 1:1 mm A001         |