





RoHS Compliant




NOTES:  
 1.MATERIAL:  
 HOUSING: HIGH TEMPERATURE THERMOPLASTIC  
 UL94V\_0,COLOR:BLACK.  
 CONTACT: COPPER ALLOYS.  
 2.PLATING:  
 UNDERPLATE: NICKEL 50u"  
 CONTACT AREA: 80u" TIN OVER NICKEL.  
 3.ELECTRICAL CHARACTERISTICS:  
 VOLTAGE RATING: 50V(MAX)  
 CURRENT RATING: 0.5A(MAX)



PIN	DIM A	DIM B	DIM C
6	2.5	7.05	3.56
8	3.5	8.05	4.56
10	4.5	9.05	5.56
12	5.5	10.05	6.56
14	6.5	11.05	7.56
16	7.5	12.05	8.56
18	8.5	13.05	9.56
20	9.5	14.05	10.56
22	10.5	15.05	11.56
24	11.5	16.05	12.56
26	12.5	17.05	13.56
28	13.5	18.05	14.56
30	14.5	19.05	15.56
32	15.5	20.05	16.56

PIN	DIM A	DIM B	DIM C
34	16.5	21.05	17.56
36	17.5	22.05	18.56
38	18.5	23.05	19.56
40	19.5	24.05	20.56
42	20.5	25.05	21.56
44	21.5	26.05	22.56
46	22.5	27.05	23.56
48	23.5	28.05	24.56
50	24.5	29.05	25.56
52	25.5	30.05	26.56
54	26.5	31.05	27.56
56	27.5	32.05	28.56
58	28.5	33.05	29.56
60	29.5	34.05	30.56



深圳市敏连达科技有限公司 Shenzhen Minlianda Technology Co.,Ltd.		品名 (ITEM NO)	0.5PH 2.6H 前插后压FPC		
		料号 (PART NO)	MLD-FPC-05-XX-H26		
单位 (UNIT): MM	未注公差 TOLERANCE UNSPECIFIED	版次 (REV): A/O	页次 (PAGE): 1/1	设计 (DESIGN)	柯南
比例 (SCALE) 1:1	X.X ± 0.38 X.XX ± 0.20 X.XXX ± 0.10 X' ± 5' X.X' ± 2'	模号 (MODEL NO)		审核 (CHECKED)	邱敏
		图号 (DWG NO)	MLD-2509031032	核准 (APPROVED)	陈镇