







RoHS Compliant

尺寸表

PIN	DIM A	DIM B	DIM C
6	2.5	3.6	8.6
8	3.5	4.6	9.6
10	4.5	5.6	10.6
12	5.5	6.6	11.6
14	6.5	7.6	12.6
16	7.5	8.6	13.6
18	8.5	9.6	14.6
20	9.5	10.6	15.6
22	10.5	11.6	16.6
24	11.5	12.6	17.6
26	12.5	13.6	18.6
28	13.5	14.6	19.6
30	14.5	15.6	20.6
32	15.5	16.6	21.6
34	16.5	17.6	22.6
36	17.5	18.6	23.6
38	18.5	19.6	24.6
40	19.5	20.6	25.6
42	20.5	21.6	26.6
44	21.5	22.6	27.6



NOTES:

- MATERIAL:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC
UL94V_0, COLOR: BLACK.
CONTACT: COPPER ALLOYS.
- PLATING:
UNDERPLATE: NICKEL 50u"
CONTACT AREA: 80u" TIN OVER NICKEL.
- MULTIMEDIA CARD COMPATIBLE

深圳市敏连达科技有限公司 Shenzhen Minlianda Technology Co.,Ltd.		品名 (ITEM NO)	0.5PH 2.0H 立贴抽拉		
		料号 (PART NO)	MLD-FPC-05L-XX-H20		
单位 (UNIT): MM	未注公差 TOLERANCE UNSPECIFIED	版次 (REV): A/0	页次 (PAGE): 1/1	设计 (DESIGN)	柯南
比例 (SCALE) 1:1	X.X ± 0.38 X.XX ± 0.20 X.XXX ± 0.10 X' ± 5' X.X' ± 2'	模号 (MODEL NO)	审核 (CHECKED)		邱敏
图号 (DWG NO)		MLD-2509031032	核准 (APPROVED)		陈镇