






RoHS Compliant



PIN	DIM A	DIM B	DIM C
6	3.56	4.5	7.2
8	4.56	5.5	8.2
10	5.56	6.5	9.2
12	6.56	7.5	10.2
14	7.56	8.5	11.2
16	8.56	9.5	12.2
18	9.56	10.5	13.2
20	10.56	11.5	14.2
22	11.56	12.5	15.2
24	12.56	13.5	16.2
26	13.56	14.5	17.2
28	14.56	15.5	18.2
30	15.56	16.5	19.2
32	16.56	17.5	20.2
34	17.56	18.5	21.2
36	18.56	19.5	22.2
38	19.56	20.5	23.2
40	20.56	21.5	24.2
42	21.56	22.5	25.2
44	22.56	23.5	26.2
46	23.56	24.5	27.2
48	24.56	25.5	28.2
50	25.56	26.5	29.2
52	26.56	27.5	30.2
54	27.56	28.5	31.2
56	28.56	29.5	32.2
58	29.56	30.5	33.2
60	30.56	31.5	34.2

NOTES:

1.MATERIAL:

HOUSING: HIGH TEMPERATURE THERMOPLASTIC
UL94V_0,COLOR:BLACK.

CONTACT: COPPER ALLOYS.

2.PLATING:

UNDERPLATE: NICKEL 50u"

CONTACT AREA: 80u" TIN OVER NICKEL.

3.ELECTRICAL CHARACTERISTICS:

VOLTAGE RATING: 50V(MAX)

CURRENT RATING: 0.5A(MAX)

深圳市敏连达科技有限公司 Shenzhen Minlianda Technology Co.,Ltd.		品名 (ITEM NO)	0.5PH 5.2H 立贴掀盖		
		料号 (PART NO)	MLD-FPC-05LF-XX-H52		
单位 (UNIT): MM	未注公差 TOLERANCE UNSPECIFIED	版次 (REV): A/O	页次 (PAGE): 1/1	设计 (DESIGN)	柯南
比例 (SCALE) 1:1	X.X ± 0.38 X.XX ± 0.20 X.XXX ± 0.10 X' ± 5' X.X' ± 2'	模号 (MODEL NO)		审核 (CHECKED)	邱敏
		图号 (DWG NO)	MLD-2509031032	核准 (APPROVED)	陈镇