


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		图面升级整理图面	2025.05.22	阿树
A2	N/A	Ⓐ2X1	产品尺寸变更	2025.09.05	阿树



Specifications:

规格:

- 1.Voltage rating:250VAC/DC
额定电压: 250V AC/DC
- 2.Current rating:3A AC/DC
额定电流: 3A AC/DC
- 3.Withstanding voltage:500V AC/minute
耐受电压: 500V AC/分钟
- 4.Temperature range: -55°C~+105°C
温度范围: -55°C~+105°C
- 5.Insulation resistance:1000MΩ MIN
绝缘电阻: 1000MΩ MIN
- 6.Contact resistance:30mΩ Max
接触电阻: 30mΩ Max

Material:



- 材料:
- 7.Rubber core:PBT UL94V-0
胶芯: PBT UL94V-0
 - 8.The iron shell:SPCC-SD Nivkel Plating/Tin Plating/Gold Plating
铁壳: SPCC-SD,镀镍/镀锡/镀金
 - 9.Terminal:Copper alloy
端子: 铜合金

PART NO.:

X01 15 F C 2 W 1
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series NO.
- ②Row No.Pin No.XX-09;15;25;37
- ③Welding Board Angle :F-Female
- ④T: Tradutional C: Car-pin
- ⑤Planting Category: 1:1U' 2:2U' 3:3U' 4:5U' 5:15U' 6:30U' 7:AuSn'
- ⑥Color:B-BLACK W-White BL-Blue
- ⑦1:TYPE-1; 2:TYPE-2; 3:TYPE-3; 4:TYPE-4

NUMBER OF POSITIONS	DIMENSION			
	A±0.25	B±0.13	C±0.38	D±0.25
9	16.35	24.99	30.80	19.28
15	24.75	33.30	39.20	27.65
25	38.35	47.04	53.05	41.28
37	54.75	63.50	69.40	57.71



铜合方式	TYPE-1:铜合	TYPE-2:前铆实心螺母	TYPE-3:后铆空心螺母	TYPE-4:后铆空心螺母锁螺丝
图示				

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAuCES	



DESIGN	阿树	VIEW:	MODEL TYPE: D-SUB
CHECKED		UNIT: mm/in	PART NO.: X0115FC2W1
APPROVED		SIZE: A4	DWG NO.: X-X0115FC2W1