



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A	(A)X8		2025.06.11	



- Specifications
- Voltage rating:250V AC,DC
 - Current rating:5A AC,DC
 - Withstanding voltage:1500V AC/minute
 - Temperature range:-45° to+125°
 - Insulation resistance: 1000MΩ Min
 - Contact resistance:≤20mΩ Max

PART NO.:

X3025 I F-P XX


Series Number.

Category: T-terminal


Category:F-Female Terminal

Material: P-Phosphor Bronze

Plating Category:SN-Bright tin plating



SECTION A-A
SCALE 1:1



SECTION B-B
SCALE 1:1

X3025TF-PSN	Phosphor Bronze	AWG#22-24	X3025HM
PART NO	Material	Wire Range	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	
CHECKED	
APPROVED	

VIEW:

UNIT: mm/in

SIZE: A4

MODEL TYPE:
3.00mm Crimp Style Connectors

PART NO.:
X3025TF-PSN

DWG NO.: