



| STRUCTURE (构造) | | | |
|----------------|-----------------------|---------------------|---------------|
| NO. | ITEM (项目) | SPECIFICATION (规格) | |
| 1 | INSULATION (胶膜) | 印字膜:通用版20624 (43μm) | |
| | | 白膜:80° C 60V (43μm) | |
| 2 | SUPPORTING TAPE (补强板) | 225μm | Blue (蓝色) |
| 3 | CONDUCTOR (导体) | Thickness (厚度) | 0.035 ±0.005 |
| | | Width (宽度) | 0.3 ±0.03 |
| 4 | CONDUCTOR (导体镀层) | PLATED (电镀) | 锡Sn (1μm) MIN |
| | | PLATED (电镀) | |

| DIMENSION (尺寸) | | | |
|--------------------------------|----|-----------|------------------|
| No. of conductors (导体数目) | N | (N) P | |
| Pitch (间距) | P | 0.5 | ±0.05 |
| Span (总间距) | SP | (N-1)*0.5 | ±0.05 |
| Width (总宽度) | W | (N+1)*0.5 | ±0.08 |
| Margin (边缘宽度) | M | 0.5 | ±0.07 |
| Total length (总长度) | TL | (TL) | ±2.0 |
| Insert Thickness (插接端厚度) | T | 0.3 | ±0.03 |
| Surface Thickness (线身厚度) | ST | 0.12 | ±0.03 |
| Strip Length (裸铜长度) | S1 | 4.0 | 4/3可定做 ±0.5 |
| | S2 | 4.0 | 4/3可定做 ±0.5 |
| Supporting Tape Length (补强板长度) | B1 | 6.0 | 8/6/5/4/可定做 ±1.0 |
| | B2 | 6.0 | 8/6/5/4/可定做 ±1.0 |

技术要求:

- 1、保存环境: 温度15~25℃ 湿度: 30~50RH%
- 2、保质期: 镀金: 12个月 镀锡: 6个月
- 3、产品符合ROHS 2.0标准

| | | | | |
|-----------|----------------------------------|----------|------------|--|
| DESIGN: | Xiping Huang | | | 广东国连电子有限公司 GUANGDONG GUOLIAN ELECTRONICS CO., LTD |
| CHECK: | Ke Tian | | | |
| APPROVED: | Youquan Xu | | | |
| TITLE: | FFC CABLE B型 | | | |
| PART NO. | 0.5*NP*TL*B(4/4/8/8) (0.035*0.3) | | | |
| REV. A | SCALE: N/A | UNIT: mm | SHEET: 1/1 | |