


Feb.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



Part No.	Cable color
~088*1T~	GRAY
~088*2T~	BLACK

NOTE ① We indicate the length of the harness on the last of product name. 'L' part.


② Tolerance for [L]

Length L [mm]	Tolerance [mm]
$35 \leq L \leq 200$	± 4
$200 < L \leq 500$	± 8
$500 < L \leq 1000$	± 12
$L > 1000$	$\pm 1.5\%$

③ Connector rotation angle is within ± 45 degree from the above image.
 For long length in the case of $L > 500$, the angle is optional.

4. Specifications are subject to change without notice.

【 DIMENSIONS OF CONNECTOR 】



1	U. FL-LP-088HF(06)	CL331-0560-8-06	2	1.37 Dia. coaxial cable
NO.	PART NO.	CODE NO.	NO.	PART NO.

HALOGEN FREE

UNITS mm		SCALE FREE	COUNT 	DESCRIPTION OF REVISIONS DIS-D-00003261	DESIGNED MS. MATSUMOTO	CHECKED MT. KANEKO	DATE 18.06.21
-------------	--	---------------	-----------	--	---------------------------	-----------------------	------------------

HRS HIROSE ELECTRIC CO., LTD.	APPROVED :NK. NINOMIYA	16.07.25	DRAWING NO. PART NO. CODE NO.	U. FL-2LPHF6-088**T-A-L	
	CHECKED :MT. KANEKO	16.07.25			
	DESIGNED :MS. MATSUMOTO	16.07.25			
	DRAWN :MS. MATSUMOTO	16.07.25			