



PC Board Layout
Component Side Shown

NOTES:

MATERIAL:

- 1. HOUSING MATERIAL : GLASS FILLED POLYESTER UL94V-0.
- 2. CONTACT MATERIAL : PHOSPHOR BRONZE ϕ 0.46mm.
- 3. PLATING : SELECTING GOLD PLATING NICKEL

ELECTRICAL :

- 1. VOLTAGE RATING : 125 VAC RMS.
- 2. CURRENT RATING : 1.5 AMP.
- 3. CONTACT RESISTANCE : 30 MILLIOHMS MAX.
- 4. INSULATION RESISTANCE : 500 MEGOHMS MIN @ 500V DC
- 5. DIELECTRIC WITHSTANDING RESISTANCE : 1000V AC RMS 50Hz. 1MIN.

MECHANICAL :

- 1. DURRABILITY : 750 CYCLES MIN:
- 2. PCB RETENTION PRE-SOLDER : 1 LB MIN

ENVIRONMENTAL :

- 1. STORAGE : -40°C TO 85°C
- 2. OPERATION : -25°C TO 85°C.

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: 网口插座 RJ45-8P/8C 52E 1*2 双胞胎 直插 带屏蔽 无灯无弹			
DRAWN: LYF	DATE: 2011-01-13	PART. NO.	R-RJ45S08P-B200		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-RJ45-0031	REV.	A