









RoHS Compliant



1: 材料: 黑色硅胶, 符合ROHS环境管理物质.
2: 尺寸: 外径:10.64*4.86*1.50mm.

A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND			VBUS	CC1	D+	D-	SUB1	VBUS			GND
GND			VBUS	SUB2	D-	D+	CC1	VBUS			GND
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1

品名 TITLE	TYPE CF 16P贴板 板上四脚插 有柱 7.85L 3A 3MD 配防水圈 IPX7 编带	设计 DESIGNED BY: 刘静	比例 SCALE	1:1
料号 PART NO.:	TYPE16-N1F1-CF7850-A	审核 CHECKED BY: 张工	张数 SHEET	1/1
图号 DWG NO.:		批准 APPROVE BY: 孟生	版本 VER.	

单位 UNITS: mm	TOLERANCE (UNLESS SPECIFIED)
0.0±0.30	0.° ±10°
.00±0.20	0.° ±8°
.000±0.10	0.00° ±5°

REV	LTR	DESCRIPTION	DATE	APPROVED
		依新料号编码原则发行图面	2024.12.26	

- NOTES:
- CURRENT RATING:
3.0A MAX.
 - DIELECTRIC WITHSTAND VOLTAGE:
100VAC.
 - TEMPERATURE RANGE:
-30 °C ~ 85 °C.
 - CONTACT RESISTANCE:
40 MILLIONHM MAX.
 - INSULATION RESISTANCE:
100 MEGOHMS MIN.
 - INSERTION FORCE :
5N~20N.
 - UNMATING FORCE:
8N~20N.
 - DURABILITY:
10,000 CYCLES.
 - WATERPROOF RATING: IPX7.
 - ALL PRODUCTS COMPLY WITH RoHS ENVIRONMENTAL REQUIREMENTS.
 - MARK "▼" AS THE FOCUS, FIRST ITEM INSPECTION.
 - MARK "⊗" TO MEASURE DIMENSIONS FOR FAI.

TABLE:

A18020311044	环氧树脂			
	A18020311045	外壳	SUS304R-1/2H,T=0.20mm	Ni:50u*Min;
		内壳	SUS304R-1/2H,T=0.30mm	Ni:50u*Min;
		护套	PA9T(G.F30%)BLACK.	/
MD半成	中夹片	SUS301R-H,T=0.15mm	/	
	上排MD	B180203111009	C2680R-H,T=0.15mm	Ni:30u*Min; Au:CONTACT AREA:1u*, Solder: AREA:MATTE=1in.
	下排MD	B180203111010	C2680R-H,T=0.15mm	
	塑胶	LCP(G.F30%) BLACK.	/	
P/N	PART NAME	MATERIALS	FINISH	

东莞市高钱达电子科技有限公司
惠州市高钱达光电科技有限公司