





材质:Material:
绝缘体:Insulator: Glass filled PBT UL94V-0 , Blue
接触件:Contacts: Male-Brass, Female-Phosphor Bronze
电镀层:Plating: Contact Gold plating over Nickel
电气性能:Electrical Characteristics:
接触电阻:Contact Resistance: 30mmax. at DC 100mA
绝缘电阻:Insulator Resistance: 1000Mmin. at 50V DC
耐压:Withstanding Voltage: 1000V AC/rms 50Hz For 1 minute
工作电流:Current Rating: 2 AMP
使用温度范围:Operating Temperature: -55°C~ +105°C
电缆规格:Cable: 1.27mm (0.050") pitch flat cable
 *Standard Gold Flash



TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD					
CHECKED:	DATE:	TITLE: DML-25S 母头 兰胶 外扣三件式					
DRAWN: LYF	DATE: 2024-06-16	PART. NO.	D-DML025PF-L000				
		UNIT	mm	SCALE	free	⊕	≡
		FILE NO.	Ckmtw-DML-0007	REV.	A	QT00	