



NOTE:

- MATERIALS AND FINISHED  
 INSULATOR : LCP OR PBT+30% GF UL 94V-0,  
 SHELL : STEEL, NI FINISHED  
 CONTACT MATERIAL:BRASS, SELEVITE GOLD FINISHED  
 HARPOON:BRASS,SN FINISHED  
 RIVET: COPPER ALLOY ,NI FINISHED  
 WITH #4-40 THREADED ASSEMBLED
- ELECTRICAL CHARACTERISTICS  
 CURRENT RATING : 1.0 AMP DC  
 VOLTAGE RATING: 300 V DC  
 CONTACT RESISTANCE :20 MILLIOHMS MAX.  
 DIELECTRIC WITHSTANDING VOLTAGE : 100 V AC MIN.  
 INSULATION RESISTANCE : 5000 MEGAOHMS MIN.
- ENVIRONMENTAL  
 OPERATING TEMPERATURE: -55°C ~ +85°C  
 STORAGE TEMPERATURE:-55°C ~ +105°C
- HOW TO ORDER:



DIM A	DIM B
15.88	28.43
19.05	31.60

RECOMMENDED PCB LAYOUT THICKNESS=1.6mm  
 TOLERANCE:±0.05

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	<b>Ckmtw</b> 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: DMR-15S/DMR-15S 双胞胎 母头 半金叉锁螺丝 间距19.05			
DRAWN:	DATE:	PART. NO.	D-DMRD15PF-D001		
LYF	2024-04-12	UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-DMR-0064	REV.	A QT00