





长螺杆:2PCS



螺丝:2PCS



线夹:6 SET



螺母:2PCS

- A1:Ø5.0
- A2:Ø6.0
- A3:Ø7.0
- A4:Ø8.0
- A5:Ø10.0
- A6:Ø11.0

5	螺母	M3六角螺母	PCS	2	
4	线夹	Ø5.0-Ø11.0*12*L14.8塑胶线夹	SET	6	
3	螺丝	M3*14.0圆头螺丝	PCS	2	
2	长杆螺丝	UNC#4-40 Ø4.4*L44.0	PCS	2	
1	上下盖	锌合金上下盖 31.2*40.8	PCS	2	
项目	名称	规格型号	单位	数量	备注

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRY CO., LTD			
CHECKED:	DATE:	TITLE: DHM-9P 锌合金外壳 C款 180度出线 (含配件)			
DRAWN: HCY	DATE: 2020-04-21	PART. NO.	D-DHM009P0-C000		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-DHM-0016	REV.	A