



RECOMMENDED PCB LAYOUT THICKNESS=1.6mm
TOLERANCE:±0.05

NOTE:

- MATERIALS AND FINISHED
INSULATOR : LCP OR PBT+30% GF UL 94V-0,
SHELL : STEEL, NI FINISHED
CONTACT MATERIAL:BRASS, Electroplating G/F
HARPOON:BRASS,SN FINISHED
RIVET:COPPER ALLOY ,NI FINISHED
WITH #4-40 THREADED ASSEMBLED
- ELECTRICAL CHARACTERISTICS
CURRENT RATING : 1.0 AMP DC
VOLTAGE RATING: 300 V DC
CONTACT RESISTANCE :20 MILLIOHMS MAX.
DIELECTRIC WITHSTANDING VOLTAGE : 100 V AC MIN.
INSULATION RESISTANCE : 5000 MEGAOHMS MIN.
- ENVIRONMENTAL
OPERATING TEMPERATURE: -55°C ~ +85°C
STORAGE TEMPERATURE:-55°C ~ +105°C

DIM A	DIM B
15.88	28.40
19.05	31.60

螺丝规格

零件编号	X尺寸	L尺寸	内牙
A/C/E	4.8	7.0	4#40
B/D/F	5.8	7.0	4#40

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRY CO., LTD			
CHECKED:	DATE:	TITLE: DMR-25P/DMR-25P 双胞胎 公头 半金铆锁 间距19.05			
DRAWN: HCY	DATE: 2025-08-01	PART. NO.	D-DMRD25PM-D001		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-DMR-0086	REV.	A QT00

TOLERANCE TABLE

.0	±0.30
.00	±0.20
.000	±0.05