

**材质: Material:**

**绝缘体: Insulator:** Glass filled PBT UL94V-0 , Blue

**接触件: Contacts:** Male-Brass, Female-Phosphor Bronze

**电镀层: Plating:** Contact Gold plating over Nickel

**电气性能: Electrical Characteristics:**

**接触电阻: Contact Resistance:** 30mmax. at DC 100mA

**绝缘电阻: Insulator Resistance:** 1000Mmin. at 500V DC





**耐压: Withstanding Voltage:** 1000V AC/rms 50Hz For 1 minute

**工作电流: Current Rating:** 2 AMP

**使用温度范围: Operating Temperature:** -55°C~+105°C

**电缆规格: Cable:** 1.27mm (0.050") pitch flat cable

\*Standard Gold Flash



**TOLERANCE TABLE**

.0	±0.30
.00	±0.20
.000	±0.05

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRYCO., LTD					
CHECKED:	DATE:	TITLE: DML-25P 公头 兰胶 外扣三件式					
DRAWN: LYF	DATE: 2024-06-16	PART. NO.	D-DML025PM-L000				
		UNIT	mm	SCALE	free	⊕	≡
		FILE NO.	Ckmtw-DML-0006	REV.	A	QT00	