


RECOMMENDED PCB LAYOUT THICKNESS=1.6mm
TOLERANCE:±0.05



TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

DIM A	DIM B
15.88	28.40
19.05	31.60

NOTE:
1. MATERIALS AND FINISHED INSULATOR : LCP OR PBT+30% GF UL 94V-0, SHELL : STEEL, NI FINISHED CONTACT MATERIAL:BRASS, Electroplating G/F HARPON:BRASS,SN FINISHED RIVET: COPPER ALLOY ,NI FINISHED WITH #4-40 THREADED ASSEMBLED
2. ELECTRICAL CHARACTERISTICS
CURRENT RATING : 3.0 AMP DC
VOLTAGE RATING: 250 V DC
CONTACT RESISTANCE : 20 MILLIOHMS MAX.
DIELECTRIC WITHSTANDING VOLTAGE : 100 V AC MIN.
INSULATION RESISTANCE : 5000 MEGAOHMS MIN.
3. ENVIRONMENTAL
OPERATING TEMPERATURE: -55°C ~ +85°C
STORAGE TEMPERATURE:-55°C ~ +105°C

螺丝规格

零件编号	X尺寸	Y尺寸	内牙
A/C/B	4.8	7.0	4#10
B/D/F	5.8	7.0	4#10

APPROVED:	DATE:	C 深圳市灿科盟实业有限公司 kmtw CHANKEMENG INDUSTRYCO., LTD
CHECKED:	DATE:	
DRAWN:	DATE:	TITLE: DMR-25P/DMR-25S 上公下母 半金铆锁 间距19.05
HCY	2025-08-01	PART. NO. D-DMRD25PM-D002
		UNIT mm SCALE Free
		FILE NO. Ckmtw-DMR-0084 REV. A QT00