



P.C.B LAYOUT

**MATERIALS AND FINISH**

SHELL : STEEL MATERIAL, NICKEL FINISHED  
 INSULATOR : PBT THERMOPLASTIC, 30% GLASS  
 FILLED, UL 94V-0 RATED, BLACK COLOR  
 CONTACT MATERIAL : BRASS  
 CONTACT FINISH : SELECTIVE GOLD FLASH  
 GROUNDING BRACKET : ZINC ALLOY, ZINC PLATED

**ELECTRICAL CHARACTERISTICS**

CONTACT CURRENT RATING : 1.0 AMPS  
 CONTACT RESISTANCE : 20 MILLIOHMS MAX.  
 DIELECTRIC WITHSTANDING VOLTAGE : 500 V AC MIN.  
 INSULATION RESISTANCE : 1000 MEGAOHMS MIN.  
 TEMPERATURE RATING : -55°C ~ +105°C

**螺丝规格**

零件编号	X尺寸	L尺寸	内牙
A/C/E	4.8	7.0	4#40
B/D/F	5.8	7.0	4#40

APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: DMR-25F/DMR-25F 双胞胎 母头 半金铆锁 间距19.05			
DRAWN: HCY	DATE: 2025-08-01	PART. NO.	D-DMRD25PF-D001		
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-DMR-0085	REV.	A

**TOLERANCE TABLE**

.0	±0.30
.00	±0.20
.000	±0.05