



| REVISIONS | | | | | |
|-----------|---------|----------|------------------|------------|--------|
| REV. | ECN NO. | LOCATION | DESCRIPTION | DATE | DESIGN |
| A0 | N/A | | INITIAL RELEASE | / | / |
| A1 | N/A | | 新增螺母规格, 图面升级整理图面 | 2025.07.26 | 阿树 |



Specifications:

规格:

- 1.Voltage rating:250VAC/DC
额定电压: 250V AC/DC
- 2.Current rating:3A(T) / 5A(C) AC/DC
额定电流: 3A(T) / 5A(C) AC/DC
- 3.Withstanding voltage:500V AC/minute
耐受电压: ≥500V AC/分钟
- 4.Temperature range: -55°C +105°C
温度范围: -55°C +105°C
- 5.Insulation resistance:1000MΩMIN
绝缘电阻: ≥1000MΩ
- 6.Contact resistance:30mΩMax
接触电阻: ≥30mΩ

Material:

材料:



- 7.Rubber core:PBT UL94V-0
胶芯: PBT UL94V-0
 - 8.The iron shell:SPCC Nivkel Plating/Tin Plating/Gold Plating
铁壳: SPCC, 镀镍/镀锡/镀金
- B、成品不能有弯针, R角不一致等不良。

PART NO.:

X02 15 W I Z W 5
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series NO.
- ②Row No.Pin No.XX-09;15;25;37
- ③Welding Board Angle :W-Male
- ④T: Tradutional C: Car-pin
- ⑤Planting Category: 1:1U' 2:2U' 3:3U' 4:5U' 5:15U' 6:30U' 7:AuSn
- ⑥Color:B-BLACK W-White BL-Blue
- ⑦1:TYPE-1; 2:TYPE-2; 5:TYPE-5; 7:TYPE-7 6:TYPE-6

| NUMBER OF POSITIONS | DIMENSION | | | |
|---------------------|-----------|--------|--------|--------|
| | A±0.25 | B±0.13 | C±0.38 | D±0.25 |
| 9 | 30.80 | 24.99 | 18.00 | 19.28 |
| 15 | 39.20 | 33.32 | 26.50 | 27.51 |
| 25 | 53.05 | 47.04 | 40.00 | 41.28 |
| 37 | 69.40 | 63.50 | 56.60 | 57.71 |



| 铆合方式 | TYPE-1:铆合 | TYPE-2:前铆实心螺母 | TYPE-7:后铆鱼叉 | TYPE-5:铆鱼叉锁螺丝 | TYPE-6:铆鱼叉锁螺丝 |
|------|-----------|---------------|-------------|---------------|---------------|
| 图示 | | | | | |

| | |
|------------------------|-------|
| AuGLAR | ±5° |
| X. | ±0.40 |
| X.x | ±0.30 |
| X.xx | ±0.20 |
| X.xxx | ±0.15 |
| UNSPECIFIED TOLERAuCES | |



| | | | | | |
|----------|----|-------|-------|-------------|--------------|
| DESIGN | 阿树 | VIEW: | | MODEL TYPE: | D-SUB |
| CHECKED | | UNIT: | mm/in | PART NO.: | X0215WT7W5 |
| APPROVED | | SIZE: | A4 | DWG NO.: | X-X0215WT7W5 |