



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

SPECIFICATIONS
 Current Rating: 3Amps
 Insulation Resistance: 1000MΩ Min
 Contact Resistance: 20mΩ Max
 Withstanding Voltage: AC 1000V
 Operation Temperature: -40°to+105°
 Contact Material: Brass
 Standard: PA6T
 Insulator Material: Polyester(UL 94V-0)
 Contact Plating: Gold Flash
 Max.Processing Temp: 240°C for30-60seconds
 (260°C for5seconds)



P/N	PIN	DIM.A	DIM.B
BX-PM2.54-1-1PWZ	1	0.00	2.54
BX-PM2.54-1-2PWZ	2	2.54	5.08
BX-PM2.54-1-3PWZ	3	5.08	7.62
BX-PM2.54-1-4PWZ	4	7.62	10.16
BX-PM2.54-1-5PWZ	5	10.16	12.70
BX-PM2.54-1-6PWZ	6	12.70	15.24
BX-PM2.54-1-7PWZ	7	15.24	17.78
BX-PM2.54-1-8PWZ	8	17.78	20.32
BX-PM2.54-1-9PWZ	9	20.32	22.86
.....
BX-PM2.54-1-40PWZ	40	(PIN-1)X2.54	(PIN)X2.54

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	BX-PM2.54-1-NPWZ	版本 REV.	A
			X.±0.30	X.*±5°	审核 CHECK	EVA		品名 TITLE	2.54FH H8.5 1xnPin 90# Y# PC3.2 PB10.2 6T	页次 SHEET	1/1
			.X±0.20	.X*±1°	核准 APPROVAL	JADE		客户料号 CUTM.NO.			
			.XX±0.10	.XX*±0.5°	单位 UNITS	MM	比例 SCALE	1:1			

