



RECOMMEND P.C.B LAYOUT  
PCB TOLERANCE:±0.05 (TOP VIEW)



SPECIFICATIONS

Current Rating:1.0 Amps  
Withstanding Voltage:AC 500V  
Insulation Resistance:1000MΩ Min  
Contact Resistance:20mΩ Max  
Operation Temperature:-40° to+105°  
Insulator Material:Polyester(UL94V-0)  
Contact Material:Brass  
Standard:PA6T  
Contact Plating:Gold Flash  
Max.Processing Temp: 240°C for30-60seconds  
(260°C for5seconds)

P/N	PIN	DIM.A	DIM.B
BX-PZ1.27-2-1PZZ	2*1	0.00	1.27
BX-PZ1.27-2-2PZZ	2*2	1.27	2.54
BX-PZ1.27-2-3PZZ	2*3	2.54	3.81
BX-PZ1.27-2-4PZZ	2*4	3.81	5.08
BX-PZ1.27-2-5PZZ	2*5	5.08	6.35
BX-PZ1.27-2-6PZZ	2*6	6.35	7.62
BX-PZ1.27-2-7PZZ	2*7	7.62	8.89
BX-PZ1.27-2-8PZZ	2*8	8.89	10.16
BX-PZ1.27-2-9PZZ	2*9	10.16	11.43
.....	.....	.....	.....
BX-PZ1.27-2-50PZZ	2*50	(PIN-1)x1.27	(PIN)x1.27

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA
			X.±0.30	X.*±5°		
.X±0.20	.X*±1°	核准 APPROVAL	JADE			
.XX±0.10	.XX*±0.5°			单位 UNITS	MM	比例 SCALE

料号 PART NO.	BX-PZ1.27-2-NPZZ	版本 REV.	A
品名 TITLE	1.27PH H1.0 2mmPin 180# W3.4 PC2.3 PA3.9 PB1.0 L7.2 6T	页次 SHEET	1/1
客户料号 CUTM.NO.			
<b>Bossie (博锡)</b>			