



RECOMMEND P.C.B LAYOUT

PCB TOLERANCE:±0.05 (TOP VIEW)

SPECIFICATIONS

Current Rating: 1.0 Amps  
 Withstanding Voltage:AC 500V  
 Insulation Resistance:1000MΩ Min  
 Contact Resistance:20mΩ Max  
 Operation Temperature:-40°to+105°  
 Insulator Material:Polyester(UL94V-0)  
 Contact Material:Phosphor bronze  
 Standard:PA6T  
 Contact Plating:Gold Flash  
 Max.Processing Temp:240°C for30-60seconds  
 (260°C for5seconds)



P/N	PIN	DIM.A	DIM.B
BX-PM1.27-2-1PU-W	2*1	0.00	1.27
BX-PM1.27-2-2PU-W	2*2	1.27	2.54
BX-PM1.27-2-3PU-W	2*3	2.54	3.81
BX-PM1.27-2-4PU-W	2*4	3.81	5.08
BX-PM1.27-2-5PU-W	2*5	5.08	6.35
BX-PM1.27-2-6PU-W	2*6	6.35	7.62
BX-PM1.27-2-7PU-W	2*7	7.62	8.89
BX-PM1.27-2-8PU-W	2*8	8.89	10.16
BX-PM1.27-2-9PU-W	2*9	10.16	11.43
.....	.....	.....	.....
BX-PM1.27-2-50PU-W	2*50	(PIN-1)x1.27	(PIN)x1.27

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA	料号 PART NO.	BX-PM1.27-2-NPU-W	版本 REV.	A
			X.±0.30	X.*±5°						
			.X±0.20	.X*±1°	核准 APPROVAL	JADE	客户料号 CUTM.NO.			
			.XX±0.10	.XX*±0.5°	单位 UNITS	MM	比例 SCALE	1:1		

