




RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)



SPECIFICATIONS

Current Rating:0.75 Amps

Withstanding Voltage:AC 500V

Insulation Resistance:1000MΩ Min

Contact Resistance:20mΩ Max

Operation Temperature:−40°to+105°

Insrlator Material:Polyester(UL94V-0)

Contact Material:Phosphor bronze

Standard:PA6T

Contact Plating:Gold Flash

Max.Processing Temp:240°C for30–60seconds
(260°C for5seconds)

P/N	PIN	DIM.A	DIM.B
BX-PZ1.0-1-1PZZ	2*1	0.00	1.00
BX-PZ1.0-1-2PZZ	2*2	1.00	2.00
BX-PZ1.0-1-3PZZ	2*3	2.00	3.00
BX-PZ1.0-1-4PZZ	2*4	3.00	4.00
BX-PZ1.0-1-5PZZ	2*5	4.00	5.00
BX-PZ1.0-1-6PZZ	2*6	5.00	6.00
BX-PZ1.0-1-7PZZ	2*7	6.00	7.00
BX-PZ1.0-1-8PZZ	2*8	7.00	8.00
BX-PZ1.0-1-9PZZ	2*9	8.00	9.00
.....			
BX-PZ1.0-1-40PZZ	2*40	(PIN-1)	(PIN)

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA			料号 PART NO.	BX-PZ1.0-1-NPZZ				版本 REV.	A
			X.±0.30	X.*±5°	审核 CHECK	EVA			品名 TITLE	1.0PH H1.0 2mPin 180# W2.3 PC2.0 PA2.0 PB1.0 L5.0 6T				页次 SHEET	1/1
			.X±0.20	.X*±1°	核准 APPROVAL	JADE			客户料号 CUTM.NO.						
			.XX±0.10	.XX*±0.5°	单位 UNITS	MM	比例 SCALE	1:1							
										 Bossie (博锡)					