



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)


SPECIFICATIONS

Current Rating: 1.5 Amps
 Insulation Resistance: 1000M Ω Min
 Contact Resistance: 20m Ω Max
 Withstanding Voltage: AC 500V
 Operation Temperature: -40°to+105°
 Contact Material: Brass
 Standard: PA6T
 Insulator Material: Polyester(UL 94V-0)
 Contact Plating: Gold Flash
 Max.Processing Temp: 240°C for 30-60seconds
 (260°C for 5 seconds)



P/N	PIN	DIM.A	DIM.B
BX-PM2.0-2-1PY	2*1	0.00	2.00
BX-PM2.0-2-2PY	2*2	2.00	4.00
BX-PM2.0-2-3PY	2*3	4.00	6.00
BX-PM2.0-2-4PY	2*4	6.00	8.00
BX-PM2.0-2-5PY	2*5	8.00	10.00
BX-PM2.0-2-6PY	2*6	10.00	12.00
BX-PM2.0-2-7PY	2*7	12.00	14.00
BX-PM2.0-2-8PY	2*8	14.00	16.00
BX-PM2.0-2-9PY	2*9	16.00	18.00
.....
BX-PM2.0-2-40PY	2*40	(PIN-1)x2.0	(PIN)x2.0

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA	料号 PART NO.	版本 REV.	A
			X.±0.30	X.*±5°					
.X±0.20	.X*±1°	核准 APPROVAL	JADE	客户料号 CUTM.NO.					
.XX±0.10	.XX*±0.5°				单位 UNITS	MM	比例 SCALE	1:1	

料号: BX-PM2.0-2-NPY
 品名: 2.0FH H4.3 2xPin 180 μ W4.5 U μ PC2.8 6T
 客户料号: 

Bossie (博锡)