



RECOMMEND P.C.B LAYOUT  
PCB TOLERANCE:±0.05 (TOP VIEW)

### SPECIFICATIONS

Current Rating: 1.5 Amps  
 Insulation Resistance: 1000MΩ Min  
 Contact Resistance: 20mΩ Max  
 Withstanding Voltage: AC 500V  
 Operation Temperature: -40° to +105°  
 Contact Material: Brass  
 Standard: PA6T  
 Insulator Material: Polyester (UL 94V-0)  
 Contact Plating: Gold Flash  
 Max. Processing Temp: 240°C for 30-60 seconds  
 (260°C for 5 seconds)



P/N	PIN	DIM.A	DIM.B
BX-PZ2.0-1-1PZZ	1	0.00	2.00
BX-PZ2.0-1-2PZZ	2	2.00	4.00
BX-PZ2.0-1-3PZZ	3	4.00	6.00
BX-PZ2.0-1-4PZZ	4	6.00	8.00
BX-PZ2.0-1-5PZZ	5	8.00	10.00
BX-PZ2.0-1-6PZZ	6	10.00	12.00
BX-PZ2.0-1-7PZZ	7	12.00	14.00
BX-PZ2.0-1-8PZZ	8	14.00	16.00
BX-PZ2.0-1-9PZZ	9	16.00	18.00
.....	.....	.....	.....
BX-PZ2.0-1-40PZZ	40	(PIN-1)x2.0	(PIN)x2.0

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA	料号 PART NO.	BX-PZ2.0-1-NPZZ	版本 REV.	A									
			X.±0.30	X.*±5°							审核 CHECK	EVA	品名 TITLE	2.0PH H2.0 1x1Pin 180K PC2.8 PA3.9 PB2.0 L8.7 6T	页次 SHEET	1/1			
			.X±0.20	.X*±1°													核准 APPROVAL	JADE	客户料号 CUTM.NO.
			.XX±0.10	.XX*±0.5°															
单位 UNITS	MM	比例 SCALE	1:1																

