



RECOMMEND P.C.B LAYOUT  
PCB TOLERANCE:±0.05 (TOP VIEW)



# SPECIFICATIONS

Current Rating: 3Amps  
 Insulation Resistance: 1000MΩ Min  
 Contact Resistance: 20mΩ Max  
 Withstanding Voltage: AC 1000V  
 Operation Temperature: -40° to +105°  
 Contact Material: Brass  
 Standard: PA6T  
 Insulator Material: Polyester(UL 94V-0)  
 Contact Plating: Gold Flash  
 Max.Processing Temp: 240°C for 30-60seconds  
 (260°C for 5seconds)

P/N	PIN	DIM.A	DIM.B
BX-PZ2.54-1-1PWZ	1	0.00	2.54
BX-PZ2.54-1-2PWZ	2	2.54	5.08
BX-PZ2.54-1-3PWZ	3	5.08	7.62
BX-PZ2.54-1-4PWZ	4	7.62	10.16
BX-PZ2.54-1-5PWZ	5	10.16	12.70
BX-PZ2.54-1-6PWZ	6	12.70	15.24
BX-PZ2.54-1-7PWZ	7	15.24	17.78
BX-PZ2.54-1-8PWZ	8	17.78	20.32
BX-PZ2.54-1-9PWZ	9	20.32	22.86
.....	.....	.....	.....
BX-PZ2.54-1-40PWZ	40	(PIN-1)X2.54	(PIN)X2.54

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA	料号 PART NO.	BX-PZ2.54-1-NPWZ	版本 REV.	A									
			X.±0.30	X.*±5°							审核 CHECK	EVA	品名 TITLE	2.54PH H2.5 1mmPin 90μ PC3.0 PA6.0 PBA.3 L13.8 6T 博	页次 SHEET	1/1			
			.X±0.20	.X*±1°													核准 APPROVAL	JADE	客户料号 CUTM.NO.
			.XX±0.10	.XX*±0.5°															

