



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

SPECIFICATIONS
 Current Rating:0.75 Amps
 Withstanding Voltage:AC 500V
 Insulation Resistance:1000MΩ Min
 Contact Resistance:20mΩ Max
 Operation Temperature:-40°to+105°
 Insulator Material:Polyester(UL94V-0)
 Contact Material:Phosphor bronze
 Standard:PA6T
 Contact Plating:Gold Flash
 Max.Processing Temp:240°C for30-60seconds
 (260°C for5seconds)

P/N	PIN	DIM.A	DIM.B
BX-PZ1.0-1-1PZZ	1	0.00	1.0000
BX-PZ1.0-1-2PZZ	2	1.0000	2.00
BX-PZ1.0-1-3PZZ	3	2.00	3.00
BX-PZ1.0-1-4PZZ	4	3.00	4.00
BX-PZ1.0-1-5PZZ	5	4.00	5.00
BX-PZ1.0-1-6PZZ	6	5.00	6.00
BX-PZ1.0-1-7PZZ	7	6.00	7.00
BX-PZ1.0-1-8PZZ	8	7.00	8.00
BX-PZ1.0-1-9PZZ	9	8.00	9.00
.....
BX-PZ1.0-1-50PZZ	50	(PIN-1)	(PIN)

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA				
			X.±0.30	X.*±5°			审核 CHECK	EVA		
			.X±0.20	.X*±1°					核准 APPROVAL	JADE
			.XX±0.10	.XX*±0.5°						

料号 PART NO.	BX-PZ1.0-1-NPZZ	版本 REV.	A
品名 TITLE	1.0PH H1.0 1mmPin 180M W1.5 PC2.0 PA2.0 PB1.0 L5.0 6T	页次 SHEET	1/1
客户料号 CUTM.NO.			
			