




SPECIFICATIONS

Current Rating: 1.5 Amps
 Insulation Resistance: 1000M Ω Min
 Contact Resistance: 20m Ω Max
 Withstanding Voltage: AC 500V
 Operation Temperature: -40° to +105°
 Contact Material: Brass
 Standard: PA6T
 Insulator Material: Polyester(UL 94V-0)
 Contact Plating: Gold Flash
 Max.Processing Temp: 240°C for 30-60seconds
 (260°C for 5seconds)



RECOMMEND P.C.B LAYOUT
 PCB TOLERANCE: ±0.05 (TOP VIEW)



P/N	PIN	DIM.A	DIM.B
BX-PZ2.0-2-1PZZ	2*1	0.00	2.00
BX-PZ2.0-2-2PZZ	2*2	2.00	4.00
BX-PZ2.0-2-3PZZ	2*3	4.00	6.00
BX-PZ2.0-2-4PZZ	2*4	6.00	8.00
BX-PZ2.0-2-5PZZ	2*5	8.00	10.00
BX-PZ2.0-2-6PZZ	2*6	10.00	12.00
BX-PZ2.0-2-7PZZ	2*7	12.00	14.00
BX-PZ2.0-2-8PZZ	2*8	14.00	16.00
BX-PZ2.0-2-9PZZ	2*9	16.00	18.00
.....
BX-PZ2.0-2-40PZZ	2*40	(PIN-1)x2.0	(PIN)x2.0

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA	料号 PART NO.	BX-PZ2.0-2-NPZZ	版本 REV.	A										
			X.±0.30	X.*±5°							审核 CHECK	EVA	品名 TITLE	2.0PH H2.0 2xPin 180 μ PC2.8 PA3.9 PB2.0 L8.7 6T	页次 SHEET	1/1				
			.X±0.20	.X.*±1°													核准 APPROVAL	JADE	客户料号 CUTM.NO.	
			.XX±0.10	.XX.*±0.5°																
						Bossie (博锡)														