



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

SPECIFICATIONS

Current Rating: 3Amps
 Insulation Resistance: 1000MΩ Min
 Contact Resistance: 20mΩ Max
 Withstanding Voltage: AC 1000V
 Operation Temperature: -40°to+105°
 Contact Material: Brass
 Standard: PA6T
 Insulator Material: Polyester(UL 94V-0)
 Contact Plating: Gold Flash
 Max.Processing Temp: 240°C for30-60seconds
 (260°C for5seconds)



P/N	PIN	DIM.A	DIM.B
BX-PM2.54-1-1PY	1	0.00	2.54
BX-PM2.54-1-2PY	2	2.54	5.08
BX-PM2.54-1-3PY	3	5.08	7.62
BX-PM2.54-1-4PY	4	7.62	10.16
BX-PM2.54-1-5PY	5	10.16	12.70
BX-PM2.54-1-6PY	6	12.70	15.24
BX-PM2.54-1-7PY	7	15.24	17.78
BX-PM2.54-1-8PY	8	17.78	20.32
BX-PM2.54-1-9PY	9	20.32	22.86
.....
BX-PM2.54-1-40PY	40	(PIN-1)X2.54	(PIN)X2.54

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE	
			X.±0.30	X.*±5°
			.X±0.20	.X.*±1°
			.XX±0.10	.XX.*±0.5°

制图 DRAWING	EMMA
审核 CHECK	EVA
核准 APPROVAL	JADE
单位 UNITS	MM
比例 SCALE	1:1

料号 PART NO.	BX-PM2.54-1-NPY	版本 REV.	A
品名 TITLE	2.54FH H8.5 1xnPin 180° Y# PC3.2 6T	页次 SHEET	1/1
客户料号 CUTM.NO.			

Bossie (博锡)