



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

SPECIFICATIONS

Current Rating: 1.5 Amps
 Insulation Resistance: 1000M Ω Min
 Contact Resistance: 20m Ω Max
 Withstanding Voltage: AC 500V
 Operation Temperature: -40°to+105°
 Contact Material: Brass
 Standard: PA6T
 Insrlator Material: Polyester(UL 94V-0)
 Contact Plating: Gold Flash
 Max.Processing Temp: 240°C for30-60seconds
 (260°C for 5 seconds)



P/N	PIN	DIM.A	DIM.B
BX-PM2.0-2-1PUW	1	0.00	2.00
BX-PM2.0-2-2PUW	2	2.00	4.00
BX-PM2.0-2-3PUW	3	4.00	6.00
BX-PM2.0-2-4PUW	4	6.00	8.00
BX-PM2.0-2-5PUW	5	8.00	10.00
BX-PM2.0-2-6PUW	6	10.00	12.00
BX-PM2.0-2-7PUW	7	12.00	14.00
BX-PM2.0-2-8PUW	8	14.00	16.00
BX-PM2.0-2-9PUW	9	16.00	18.00
.....
BX-PM2.0-2-40PUW	40	(PIN-1)x2.0	(PIN)x2.0

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA	料号 PART NO.	BX-PM2.0-2-NPUW	版本 REV.	A										
			X.±0.30	X.*±5°							审核 CHECK	EVA	品名 TITLE	2.0FH H4.3 2xnPin SMT W4.5 U# PC6.5 PB4.6 6T	页次 SHEET	1/1				
			.X±0.20	.X*±1°													核准 APPROVAL	JADE	客户料号 CUTM.NO.	
			.XX±0.10	.XX*±0.5°																

B Bossie (博锡)